

# Duo-Mix 405

## DESCRIPTION AND GENERAL PROPERTIES

- Material Neoprene and natural latex
- Interior finish Flocked
- Exterior finish Embossed texture
- Length (cm) 33
- Thickness (mm) 0.70
- Colour/Color Blue/yellow
- Wrist Straight cuff
- Size 6 7 8 9 10
- Packaging pair/bag - pairs/bag - pairs/carton



## PERFORMANCE RESULTS

Certification category 3

CE 0334



2120




### Legends



**MECHANICAL HAZARDS EN 388**

PERFORMANCE LEVELS



**LOW CHEMICAL PROTECTION EN 374**



**MICRO-ORGANISMS EN 374**




**RADIOACTIVE CONTAMINATION EN 421**



**HEAT AND FIRE EN 407**

PERFORMANCE LEVELS




**SPECIFIC CHEMICAL PROTECTION EN 374**

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofurane
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%



**COLD HAZARDS EN 511**

PERFORMANCE LEVELS



For more details: [www.mapa-pro.com](http://www.mapa-pro.com)

# Duo-Mix 405

## SPECIFIC ADVANTAGES

- Tactile sensitivity, due to the gloves reduced thickness
- Comfort and perspiration absorption, due to the cotton flock-lining
- Good grip, due to the non-slip embossing

## MAIN FIELDS OF USE

### Aeronautics industry

- Work with composite materials (resins)

### Automotive/mechanical industry

- Spray-painting

### Other industries

- Industrial cleaning, maintenance

## INSTRUCTIONS FOR USE

### Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the "CE"-type tests.
- It is not recommended for persons sensitized to natural latex, dithiocarbamates and thiazoles to use these gloves.
- Put the gloves on dry, clean hands.
- Do not use the gloves in contact with a chemical for a duration in excess of the measured breakthrough time. Refer to the website [www.mapa-pro.com](http://www.mapa-pro.com) or contact the Technical Customer Service - MAPA PROFESSIONNEL ([stc.mapaspontex@mapaspontex.fr](mailto:stc.mapaspontex@mapaspontex.fr)) in order to know this breakthrough time. Use 2 pairs alternatively when in long duration contact with a solvent.
- Turn the cuff end down in order to prevent a hazardous chemical from dripping onto the arm.
- Inspect the gloves for cracks or snags before reusing them.

### Storage conditions

- Store the gloves in their original packaging protected from direct sunlight, far from heat sources or electric equipment.

### Laundering conditions

- Before taking off the gloves, clean them as appropriate :
- in use with a solvent (alcohols, etc...) : rub over with a dry cloth
- in use with acids or alkalis : thoroughly rinse the gloves under running water, and rub over with a dry cloth
- Caution : using the gloves or submitting them to another cleaning or laundering process can alter their performance levels.

### Drying conditions

- Ensure the inside of the gloves is dry before putting them on again.

## LEGISLATION

- This product is not classified as hazardous according to the directive 1999/45/EC of the European Parliament and of the Council.
- This product does not contain any substances of very high concern according to the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- CE-Type Examination Certificate 0075/014/162/11/10/0469
- Issued by the notified body nr 0075  
C.T.C. – 4 rue Hermann Frenkel - F- 69367 LYON Cedex 07
- Quality assurance certificat O334 Asqual 14 rue des Reculettes -F-75013 PARIS